

Product data sheet

Characteristics

8702SBT49V06

Reversing Contactor, Size 0, 3-Pole, NEMA 7/9

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 3,716.00 USD



Main

Product	Contactator
Type	Type S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Contactator Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	0

Environment

Enclosure Type	NEMA 7/9 cast aluminium type: bolted
Product certifications	CSA UL listed

Ordering and shipping details

Category	21281 - 8702,36 S*R,S*T,S*W
----------	-----------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	18.900000000000002
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------