

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 1,229.00 USD



### Main

Product	Contacteur
Type	Type S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	208 V AC 60 Hz
Contacteur Type	Reversing
Number of Poles	2P
Phase	1 phase
Motor Wiring	3 wires
Line Rated Current	27 A
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	1
Height	11.89 in (302 mm)
Depth	7.4 in (188 mm)
Width	11.89 in (302 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed

### Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	20.23
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

### Contractual warranty

Warranty period	18 months
-----------------	-----------