

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,259.00 USD



Main

Product	Contacteur
Type	Type S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Contacteur Type	Reversing
Motor type	Repulsion induction
Number of Poles	3P
Phase	1 phase
Motor Wiring	4 wires
Line Rated Current	27 A
Horsepower Rating	3 HP 230 V AC 2 HP 115 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	1
Height	11.89 in (302 mm)
Depth	7.4 in (188 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA UL listed

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	20.23
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------