

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 1, 3-Pole, NEMA 1 +Options

8702SCG8V06C20

Price*: 1,593.00 USD

Discontinued

Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

Complementary

Nema Size	1
Rated Current	27 A
Number Of Poles	4P
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
Coil Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	Selector switch (FORWARD-REVERSE)
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	11.89 in (302 mm)
Width	11.89 in (302 mm)
Depth	7.40 in (188 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
Certifications	CSA UL Listed

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	20.56 lb(US) (9.326 kg)

Contractual warranty

Warranty	18 months
----------	-----------