

# 8702SCG8V80FF4T

## Reversing Contactor, Size 1, 3-Pole, NEMA 1 +Options



Price\* : 1,956.00 USD



8702SCG8V80FF4T has not been replaced. Please contact your customer care center for more information.

### Main

Product	Contactator
Type	Type S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	240 V (primary), 120 V (secondary)
Contactator Type	Reversing
Number of Poles	4P
Phase	3 phases
Line Rated Current	27 A
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary), 1 fuse (secondary)
Electrical connection	Screw clamp terminals
NEMA size	1
Height	11.89 in (302 mm)
Depth	7.4 in (188 mm)
Width	11.89 in (302 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	UL listed CSA

## Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	26.100000000000001
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------