

8702SCO7V02SX1100

Reversing Contactor, Size 1, 3-Pole, Vertical Open Style +Options



Price* : 1,484.00 USD



8702SCO7V02SX1100 has not been replaced. Please contact your customer care center for more information.

Main

Product	Contactator
Type	Type S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Contactor Type	Reversing
Number of Poles	4P
Phase	3 phases
Line Rated Current	27 A
Horsepower Rating	7.5 HP 200 V AC 7.5 HP 230 V AC 10 HP 460 V AC 10 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Auxiliary Contacts	1 NO + 1 NC for forward direction
Electrical connection	Screw clamp terminals
NEMA size	1
Height	9.21 in (234 mm)
Depth	5.31 in (135 mm)
Width	6.42 in (163 mm)

Environment

Enclosure Type	Not rated (open device)
Orientation	Vertical

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	11
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------