

# Product data sheet

Specifications

SQUARE D



REV MAG CONT, SIZE 1, OPEN,  
240V/60HZ

8702SCO8V03

! Discontinued

## Main

Device Short Name	S
-------------------	---

## Complementary

Line Rated Current	27 A
Depth	5.31 in (134.87 mm)
Height	5 in (127.00 mm)
Maximum Horse Power Rating	7.5 hp 200/230 V AC 10 hp 460/575 V AC
Mounting Support	horizontal support
Nema Size	1
Number Of Poles	3
Net Weight	12 lb(US) (5.44 kg)
Width	7.13 in (181.10 mm)

## Environment

Product Certifications	UL listed file E78351 CCN NLDX CSA LR60905 class 3211 04
------------------------	---

## Ordering and shipping details

Category	21272-8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	11.00 lb(US) (4.99 kg)

## Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications