

Product data sheet

Specifications

SQUARE D



Reversing Contactor, Size 2, 3-Pole, Horizontal Open Style +Options

8702SDO2V02SX1200

Price*: 2,691.00 USD

! Discontinued

Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

Complementary

Nema Size	2
Rated Current	45 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Auxiliary Contacts	1 NO + 2 NC forward
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	6.89 in (175 mm)
Width	10.04 in (255 mm)
Depth	6.02 in (153 mm)

Environment

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
-------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	16.00 lb(US) (7.257 kg)

Contractual warranty

Warranty	18 months
----------	-----------