

8702SDO2V08

Reversing Contactor, Size 2, 3-Pole, Horizontal Open Style

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 2,222.00 USD



Main

Product	Contacteur
Type	Type S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	208 V AC 60 Hz
Contacteur Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	45 A
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	Fuse not supplied
Electrical connection	Screw clamp terminals
NEMA size	2
Height	6.89 in (175 mm)
Depth	6.02 in (153 mm)
Width	9.02 in (229 mm)

Environment

Enclosure Type	Not rated (open device)
Orientation	Horizontal

Product certifications	CSA UL listed
------------------------	------------------

Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	16
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

Contractual warranty

Warranty period	18 months
-----------------	-----------
