


# 8702SDO2V81F4T

Reversing Contactor, Size 2, 3-Pole, Horizontal  
Open Style +Options



Price\* : 2,763.00 USD



8702SDO2V81F4T has not been replaced. Please contact your customer care center for more information.

## Main

Product	Contactator
Type	Type S
Control Circuit Type	Control circuit transformer

## Complementary

Control Circuit Voltage	480 V (primary), 120 V (secondary)
Contactor Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	45 A
Horsepower Rating	10 HP 200 V AC 15 HP 230 V AC 25 HP 460 V AC 25 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary)
Electrical connection	Screw clamp terminals
NEMA size	2

## Environment

Enclosure Type	Not rated (open device)
Orientation	Horizontal
Product certifications	CSA UL listed

## Ordering and shipping details

Category	21272 - 8702,36 SC,SD(NOT S*R,T,W)
----------	------------------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	19.77
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

### Contractual warranty

Warranty period	18 months
-----------------	-----------