

# Product data sheet

Specifications

SQUARE D



## Reversing Contactor, Size 4, 3-Pole, Vertical Open Style +Options

8702SFO1V02SX1010

Price\*: 9,516.00 USD

! Discontinued

### Main

Product Type	Contactor
Product Range	Type S
Contactor Type	Reversing

### Complementary

Nema Size	4
Rated Current	135 A
Number Of Poles	3P
Mounting Orientation	Vertical
Maximum Voltage Rating	600 V AC
Phase	3 phase
Horsepower Rating	40 HP 200 V AC 50 HP 230 V AC 100 HP 460 V AC 100 HP 575 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Auxiliary Contacts	1 NO reverse 1 NO forward
Other Equipment	Fuse not supplied
Terminal Type	Screw clamp terminals
Height	23.90 in (607 mm)
Width	7.95 in (202 mm)
Depth	7.01 in (178 mm)

### Environment

Enclosure Type	Not rated (open device)
Certifications	CSA UL Listed

### Ordering and shipping details

Discount Schedule	CP1
-------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Returnability	No
Country Of Origin	US

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	96.00 lb(US) (43.545 kg)

## Contractual warranty

Warranty	18 months
----------	-----------