


8702SGW11V02S

REVERSING CONTACTOR 600VAC 270A

NEMA



Price* : 24,017.00 USD



8702SGW11V02S has not been replaced. Please contact your customer care center for more information.

Main

Control circuit	Separate control circuit
Device short name	S
Enclosure type	Enclosure water resistant indoor/outdoor Enclosure dustproof indoor/outdoor Enclosure corrosion resistance indoor/outdoor

Complementary

[In] rated current	270 A
System Voltage	120 V AC 60 Hz 110 V AC 50 Hz
Depth	12.13 in
Device mounting	Surface
Electrical connection	Screw clamp terminal
Enclosure material	Brushed stainless steel
Height	49.22 in
Motor power hp	200 hp 460/575 V AC 100 hp 230 V AC 75 hp 200 V AC
NEMA size	5
Network number of phases	3 phases
Number of poles	3
Permissible voltage	<= 600 V AC
Product weight	300 lb(US)
Width	35.22 in

Environment

NEMA degree of protection	NEMA 4/4X
Product certifications	UL listed file E78351 CCN NLDX

Ordering and shipping details

Category	21282 - 8702,36 W/STAINLESS ENCLOSURES
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	276
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------