

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 953.00 USD



### Main

Product	Starter
Type	S
Control Circuit Type	Common control circuit

### Complementary

Control Circuit Voltage	208 V AC 60 Hz
Starter Type	Reversing
Motor type	Split phase
Number of Poles	3P
Phase	1 phase
Motor Wiring	4 wires
Line Rated Current	9 A
Horsepower Rating	0.33 HP 115 V AC 1 HP 230 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Melting alloy 1 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	00
Height	11.89 in (302 mm)
Depth	7.52 in (191 mm)
Width	11.89 in (302 mm)

### Environment

Enclosure Type	NEMA 1 painted sheet steel
Product certifications	CSA

NEMA  
UL listed

---

### Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	23.510000000000002
Returnability	N
Country of origin	MX

---

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

---

### Contractual warranty

Warranty period	18 months
-----------------	-----------

---