

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 00, 9A, 2 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 120 VAC coil, NEMA 1

8736SAG16V81F4T

! Discontinued

Price*: 989.00 USD

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	00
Rated Current	9 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Melting alloy 3
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
Scrr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Control Circuit Type	Control circuit transformer
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Other Equipment	2 fuses (primary)
Terminal Type	Screw clamp terminals
Height	11.88 in (301.75 mm)
Width	11.88 in (301.75 mm)
Depth	7.53 in (191.26 mm)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Type	NEMA 1 painted sheet steel
Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Gtin	785901570523
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	50.00 lb(US) (22.68 kg)

Contractual warranty

Warranty	18 months
----------	-----------