


8736SAO16V02H318S

Reversing Starter Size 00, 3-Pole, Motor Logic SSOLR +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,074.50 USD



Main

Product	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	9 A
Horsepower Rating	1.5 HP 200 V AC 1.5 HP 230 V AC 2 HP 460 V AC 2 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Solid state Motor Logic class 10/20
Electrical connection	Screw clamp terminals
NEMA size	00
Height	6.93 in (176 mm)
Depth	5.31 in (135 mm)
Width	7.13 in (181 mm)

Environment

Enclosure Type	Not rated (open device)
Orientation	Horizontal

Product certifications	CSA NEMA UL listed
------------------------	--------------------------

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901777779
Nbr. of units in pkg.	1
Package weight(Lbs)	8
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <i>Will not be compliant</i>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------