

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,986.00 USD



Main

Product	Starter
Type	S
Control Circuit Type	Common control circuit

Complementary

Control Circuit Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	3 momentary push-buttons (FORWARD-REVERSE-STOP)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	13.74 in (349 mm)
Depth	7.76 in (197 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 12 painted sheet steel
Product certifications	CSA

NEMA
UL listed

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	18.02
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------