

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 2 HP at 230 VAC, 5 kA SSCR, 1 phase, 3 pole, melting alloy overload, 240 VAC coil, NEMA 1

8736SBG3V03A1

Discontinued

Price*: 1,692.00 USD

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	0
Rated Current	18 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Wiring Mode	4 wires
Maximum Voltage Rating	600 V AC
Phase	1 phase
Motor Type	Split phase
Type Of Overload	Melting alloy 1
Horsepower Rating	1 HP 115 V AC 2 HP 230 V AC
Sccr	Circuit-breaker: 5 kA at 600 V AC Fuse: 5 kA at 600 V AC
Coil Voltage	220 V AC 50 Hz 240 V AC 60 Hz
Control Circuit Type	Common control circuit
Control Units	3 momentary push-buttons (FORWARD-REVERSE-STOP)
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	11.88 in (301.75 mm)
Width	11.88 in (301.75 mm)
Depth	7.53 in (191.26 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel
----------------	----------------------------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Certifications	UL Listed CSA
----------------	------------------

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	23.78 lb(US) (10.786 kg)

Contractual warranty

Warranty	18 months
----------	-----------