

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, 5 kA SSCR, 3 phase, 3 pole, melting alloy overload, 24 VAC coil, NEMA 1

8736SBG4V82FF4TX1100

Discontinued

Price*: 2,169.00 USD

Main

| | |
|---------------|-----------|
| Product Type | Starter |
| Product Range | S |
| Starter Type | Reversing |

Complementary

| | |
|------------------------|---|
| Nema Size | 0 |
| Rated Current | 18 A |
| Number Of Poles | 3P |
| Maximum Voltage Rating | 600 V AC |
| Phase | 3 phase |
| Type Of Overload | Melting alloy 3 |
| Horsepower Rating | 3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC |
| Coil Voltage | 240 V AC 60 Hz primary circuit 24 V AC 60 Hz secondary circuit |
| Control Circuit Type | Control circuit transformer |
| Control Units | No control units |
| Auxiliary Contacts | 1 NO + 1 NC forward |
| Other Equipment | 1 fuse (primary), 1 fuse (secondary) |
| Terminal Type | Screw clamp terminals |
| Height | 11.89 in (302 mm) |
| Width | 11.89 in (302 mm) |
| Depth | 7.52 in (191 mm) |

Environment

| | |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | UL Listed CSA NEMA |

Ordering and shipping details

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | US |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|