

8736SBO10V01S

Reversing Starter Size 0, 3-Pole, Melting Alloy Overload, Vertical Open +Options

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 1,097.00 USD



Main

Product	Starter
Type	S
Control Circuit Type	Separate control circuit

Complementary

Control Circuit Voltage	24 V AC 60 Hz
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0
Height	11.54 in (293 mm)
Depth	5.31 in (135 mm)
Width	5.39 in (137 mm)

Environment

Enclosure Type	Not rated (open device)
Orientation	Vertical

Product certifications	CSA NEMA UL listed
------------------------	--------------------------

Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901874218
Nbr. of units in pkg.	1
Package weight(Lbs)	8
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <i>Will not be compliant</i>
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------