

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 0, 18A, 5 HP at 575 VAC, up to 100 kA SCCR, 3 phase, 3 pole, Motor Logic SSOLR, 240 VAC coil, open

8736SBO4V03H20

! Discontinued

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |                                                                                                                                                                                                                                  |
|------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nema Size              | 0                                                                                                                                                                                                                                |
| Rated Current          | 18 A                                                                                                                                                                                                                             |
| Number Of Poles        | 3P                                                                                                                                                                                                                               |
| Mounting Orientation   | Horizontal                                                                                                                                                                                                                       |
| Wiring Mode            | 3 wires                                                                                                                                                                                                                          |
| Maximum Voltage Rating | 600 V AC                                                                                                                                                                                                                         |
| Phase                  | 3 phase                                                                                                                                                                                                                          |
| Type Of Overload       | Solid state Motor Logic class 20                                                                                                                                                                                                 |
| Horsepower Rating      | 3 HP 200 V AC<br>3 HP 230 V AC<br>5 HP 460 V AC<br>5 HP 575 V AC                                                                                                                                                                 |
| Sccr                   | Circuit-breaker 70 A maximum: 100 kA at 480 V AC<br>Fuse J 60 A maximum: 100 kA at 600 V AC<br>Fuse T 60 A maximum: 100 kA at 600 V AC<br>Fuse RK1 60 A maximum: 100 kA at 600 V AC<br>Fuse RK5 60 A maximum: 100 kA at 600 V AC |
| Coil Voltage           | 220 V AC 50 Hz<br>240 V AC 60 Hz                                                                                                                                                                                                 |
| Control Circuit Type   | Common control circuit                                                                                                                                                                                                           |
| Control Units          | No control units                                                                                                                                                                                                                 |
| Pilot Light            | Without pilot light                                                                                                                                                                                                              |
| Auxiliary Contacts     | Without                                                                                                                                                                                                                          |
| Terminal Type          | Screw clamp terminals                                                                                                                                                                                                            |
| Height                 | 6.91 in (175.51 mm)                                                                                                                                                                                                              |
| Width                  | 7.13 in (181.10 mm)                                                                                                                                                                                                              |
| Depth                  | 5.31 in (134.87 mm)                                                                                                                                                                                                              |

## Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |                         |
|----------------|-------------------------|
| Enclosure Type | Not rated (open device) |
| Certifications | UL Listed<br>CSA        |

## Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21271-8702,36 SA,SB(NOT S*R,T,W) |
| Discount Schedule | CP1                              |
| Gtin              | 00785901789826                   |
| Returnability     | No                               |
| Country Of Origin | MX                               |

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type Of Package 1       | PCE                    |
| Number Of Units In Package 1 | 1                      |
| Package 1 Weight             | 7.58 lb(US) (3.438 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|