


# 8736SBO4V81F4T

## Reversing Starter Size 0, 3-Pole, Melting Alloy Overload,Horizontal Open+Options



Price\* : 1,481.00 USD



8736SBO4V81F4T has not been replaced. Please contact your customer care center for more information.

### Main

Product	Starter
Type	S
Control Circuit Type	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Starter Type	Reversing
Number of Poles	3P
Phase	3 phases
Line Rated Current	18 A
Horsepower Rating	3 HP 200 V AC 3 HP 230 V AC 5 HP 460 V AC 5 HP 575 V AC
System Voltage	600 V AC
Control Units	No control units
Control Circuit Fusing	2 fuses (primary)
Thermal overload type	Melting alloy 3 Thermal Units
Electrical connection	Screw clamp terminals
NEMA size	0

### Environment

Enclosure Type	Not rated (open device)
Orientation	Horizontal
Product certifications	CSA NEMA UL listed

## Ordering and shipping details

Category	21271 - 8702,36 SA,SB(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	8.75
Returnability	N
Country of origin	MX

## Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

## Contractual warranty

Warranty period	18 months
-----------------	-----------