

# Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 1, 27A, 10 HP at 575 VAC, up to 100 kA SCCR, 3 phase, 3 pole, Motor Logic SSOLR, 120 V coil, NEMA 1

8736SCG8V02H20S

Discontinued

## Main

|               |           |
|---------------|-----------|
| Product Type  | Starter   |
| Product Range | S         |
| Starter Type  | Reversing |

## Complementary

|                        |                                                                        |
|------------------------|------------------------------------------------------------------------|
| Nema Size              | 1                                                                      |
| Rated Current          | 27 A                                                                   |
| Number Of Poles        | 3P                                                                     |
| Maximum Voltage Rating | 600 V AC                                                               |
| Phase                  | 3 phase                                                                |
| Type Of Overload       | Solid state Motor Logic class 20                                       |
| Horsepower Rating      | 7.5 HP 200 V AC<br>7.5 HP 230 V AC<br>10 HP 460 V AC<br>10 HP 575 V AC |
| Coil Voltage           | 110 V AC 50 Hz<br>120 V AC 60 Hz                                       |
| Control Circuit Type   | Separate control circuit                                               |
| Control Units          | No control units                                                       |
| Terminal Type          | Screw clamp terminals                                                  |

## Environment

|                |                            |
|----------------|----------------------------|
| Enclosure Type | NEMA 1 painted sheet steel |
| Certifications | CSA<br>NEMA<br>UL Listed   |

## Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21272-8702,36 SC,SD(NOT S*R,T,W) |
| Discount Schedule | CP1                              |
| Gtin              | 00785901399698                   |
| Returnability     | No                               |
| Country Of Origin | MX                               |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

|                              |                          |
|------------------------------|--------------------------|
| Unit Type Of Package 1       | PCE                      |
| Number Of Units In Package 1 | 1                        |
| Package 1 Weight             | 25.36 lb(US) (11.503 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|