

Product data sheet

Specifications

SQUARE D



NEMA Starter, Type S, reversing, horizontal, Size 4, 135A, 100 HP at 575 VAC, up to 100 kA SCCR, 3 phase, 3 pole, Motor Logic SSOLR, 120 V coil, open

8736SFO3V02H10S

! Discontinued

Main

Product Type	Starter
Product Range	S
Starter Type	Reversing

Complementary

Nema Size	4
Rated Current	135 A
Number Of Poles	3P
Mounting Orientation	Horizontal
Wiring Mode	3 wires
Maximum Voltage Rating	600 V AC
Phase	3 phase
Type Of Overload	Solid state Motor Logic class 10
Horsepower Rating	40 HP 200 V AC 50 HP 230 V AC 100 HP 460 V AC 100 HP 575 V AC
Scrr	Circuit-breaker 225 A maximum: 100 kA at 480 V AC Fuse J 200 A maximum: 100 kA at 600 V AC Fuse T 200 A maximum: 100 kA at 600 V AC Fuse RK1 200 A maximum: 100 kA at 600 V AC Fuse RK5 200 A maximum: 100 kA at 600 V AC
Coil Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Control Circuit Type	Separate control circuit
Control Units	No control units
Pilot Light	Without pilot light
Auxiliary Contacts	Without
Terminal Type	Screw clamp terminals
Height	14.59 in (370.59 mm)
Width	14.25 in (361.95 mm)
Depth	7.00 in (177.80 mm)

Environment

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Enclosure Type	Not rated (open device)
Certifications	UL Listed CSA

Ordering and shipping details

Category	21273-8702,36 SE,SF(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	54.00 lb(US) (24.494 kg)

Contractual warranty

Warranty	18 months
----------	-----------