

8738SBA11V08

REVERSING COMBO STARTER 600VAC 18A NEM

Product availability : Non-Stock - Not normally stocked in distribution facility



Price** : 2,613.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit
Control Units	No control units
Enclosure Type	NEMA 12 painted sheet steel without external reset
Auxiliary Contacts	Without
Horsepower Rating	3 hp 200 V AC, 3 phases 3 hp 230 V AC, 3 phases 5 hp 460 V AC, 3 phases 5 hp 575 V AC, 3 phases
Number of Poles	3P
Maximum Voltage Rating	600 V AC
NEMA Size	0
Control Circuit Voltage	208 V AC 60 Hz
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	melting alloy
Number of Thermal Units Required	3
Disconnect Type	Non-fusible disconnect

Ordering and shipping details

Category	21291 - 8738,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Package weight(Lbs)	23.59 kg (52 lb(US))
Returnability	No
Country of origin	MX

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds which is known to the State of California to cause Carcinogen & Reproductive harm. For more information go to www.p65warnings.ca.gov
EU RoHS Directive	Will be compliant – Date to be confirmed

Contractual warranty

Warranty	18 months
----------	-----------
