

# Product data sheet

Specifications



## REVERSING COMBO STARTER 600VAC 18A NEM

8738SBA23V81A1F4H20T

! Discontinued

### Main

|                         |  |
|-------------------------|--|
| Product                 | Combination Starter  |
| Type                    | S  |
| Control Circuit Type    | Control circuit transformer  |
| Control Circuit Fusing  | 2 fuses primary circuit  |
| Control Units           | Push-button FORWARD)<br>Push-button REVERSE)<br>Push-button STOP)  |
| Enclosure Type          | NEMA 12 painted sheet steel with external reset                    |
| Auxiliary Contacts      | Without  |
| Horsepower Rating       | 5 hp 460 V AC, 3 phase<br>5 hp 575 V AC, 3 phase                   |
| Number Of Poles         | 3P   |
| Maximum Voltage Rating  | 600 V AC   |
| Nema Size               | 0  |
| Control Circuit Voltage | 120 V AC 60 Hz secondary circuit<br>480 V AC 60 Hz primary circuit |
| Pilot Light             | No indicator   |
| Starter Type            | Reversing  |
| Overload Type           | Motor Logic solid state class 20                                   |
| Disconnect Type         | Fusible disconnect H, 30 A   |

### Ordering and shipping details

|                   |                                  |
|-------------------|----------------------------------|
| Category          | 21291-8738,39SB(NOT S*R,S*T,S*W) |
| Discount Schedule | CP1                              |
| Returnability     | No                               |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.