

# Product data sheet

Specifications



## REVERSING COMBO STARTER 600VAC 18A NEM

8738SBG33V81A1F4P1P2T

Price\*: 3,843.00 USD

! Discontinued

### Main

|                                  |  |
|----------------------------------|--|
| Product                          | Combination Starter  |
| Type                             | S  |
| Control Circuit Type             | Control circuit transformer  |
| Control Circuit Fusing           | 2 fuses primary circuit  |
| Control Units                    | Push-button FORWARD)<br>Push-button REVERSE)<br>Push-button STOP)  |
| Enclosure Type                   | NEMA 1 painted sheet steel with external reset                     |
| Auxiliary Contacts               | Without  |
| Horsepower Rating                | 5 hp 460 V AC, 3 phase<br>5 hp 575 V AC, 3 phase                   |
| Number Of Poles                  | 3P   |
| Maximum Voltage Rating           | 600 V AC   |
| Nema Size                        | 0  |
| Control Circuit Voltage          | 120 V AC 60 Hz secondary circuit<br>480 V AC 60 Hz primary circuit |
| Pilot Light                      | Red indicator on incandescent<br>Green indicator off incandescent  |
| Starter Type                     | Reversing  |
| Overload Type                    | melting alloy  |
| Number Of Thermal Units Required | 3  |
| Disconnect Type                  | Fusible disconnect R, 30 A   |

### Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications