

Product data sheet

Specifications



REVERSING COMBO STARTER 600VAC 18A NEM

8738SBG33V86F4T

Price*: 2,604.00 USD

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer
Control Circuit Fusing	2 fuses primary circuit
Control Units	No control units
Enclosure Type	NEMA 1 painted sheet steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	5 hp 460 V AC, 3 phase 5 hp 575 V AC, 3 phase
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Nema Size	0
Control Circuit Voltage	120 V AC 60 Hz secondary circuit 600 V AC 60 Hz primary circuit
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	melting alloy
Number Of Thermal Units Required	3
Disconnect Type	Fusible disconnect R, 30 A

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	55.00 lb(US) (24.948 kg)

Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications