

8738SBW33V81A1F4T

REVERSING COMBO STARTER 600VAC 18A NEM



Price* : 4,913.00 USD



8738SBW33V81A1F4T has not been replaced. Please contact your customer care center for more information.

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer
Control Circuit Fusing	2 fuses primary circuit
Control Units	Pushbutton STOP Pushbutton FORWARD Pushbutton REVERSE
Enclosure Type	NEMA 4/4X stainless steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	5 hp 460 V AC 3 phases 5 hp 575 V AC 3 phases
Number of Poles	3P
System Voltage	600 V AC
NEMA Size	0
Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	Melting alloy
Number of Thermal Units Required	3
Disconnect Type	Fusible disconnect R 30 A

Ordering and shipping details

Category	21297 - 8738,39 W/STAINLESS ENCLOS
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	60
Returnability	N

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------
