

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 27A NEM

8738SCG14V07A1S

Price*: 2,910.00 USD

! Discontinued

Main

| | |
|----------------------------------|---|
| Product | Combination Starter |
| Type | S |
| Control Circuit Type | Separate control circuit |
| Control Units | Push-button FORWARD) Push-button REVERSE) Push-button STOP) |
| Enclosure Type | NEMA 1 painted sheet steel with external reset |
| Auxiliary Contacts | Without |
| Horsepower Rating | 10 hp 460 V AC, 3 phase 10 hp 575 V AC, 3 phase |
| Number Of Poles | 3P |
| Maximum Voltage Rating | 600 V AC |
| Nema Size | 1 |
| Control Circuit Voltage | 550 V AC 50 Hz 600 V AC 60 Hz |
| Pilot Light | No indicator |
| Starter Type | Reversing |
| Overload Type | melting alloy |
| Number Of Thermal Units Required | 3 |
| Disconnect Type | Fusible disconnect H, 30 A |

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |

Packing Units

| | |
|------------------------------|--------------------------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Weight | 55.00 lb(US) (24.948 kg) |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications