

8738SCW44V02S

REVERSING COMBO STARTER 600VAC 27A NEM

Product availability : Non-Stock - Not normally stocked in distribution facility



Price* : 4,712.00 USD



Main

Product	Combination Starter
Type	S
Control Circuit Type	Separate control circuit
Control Units	No control units
Enclosure Type	NEMA 4X glass polyester with external reset
Auxiliary Contacts	Without
Horsepower Rating	10 hp 460 V AC 3 phases 10 hp 575 V AC 3 phases
Number of Poles	3P
System Voltage	600 V AC
NEMA Size	1
Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	Melting alloy
Number of Thermal Units Required	3
Disconnect Type	Fusible disconnect R 30 A

Ordering and shipping details

Category	21296 - 8738,39 S*R,S*T,S*W
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	57
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant Will be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
----- Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
----- More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------