

# Product data sheet

Specifications

SQUARE D



## REVERSING COMBO STARTER 600VAC 45A NEM

8738SDA44V81C14FF4P1T

Price\*: 6,066.00 USD

! Discontinued

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Control Units	Selector switch FORWARD-OFF-REVERSE)
Enclosure Type	NEMA 12 painted sheet steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	25 hp 460 V AC, 3 phase 25 hp 575 V AC, 3 phase
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Nema Size	2
Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Pilot Light	Red indicator on incandescent
Starter Type	Reversing
Overload Type	melting alloy
Number Of Thermal Units Required	3
Disconnect Type	Fusible disconnect R, 60 A

### Ordering and shipping details

Discount Schedule	CP1
Returnability	No

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.