

# 8738SDA44V81C14FF4P1T

## REVERSING COMBO STARTER 600VAC 45A NEM

Price\* : 6,066.00 USD



⚠ Discontinued

8738SDA44V81C14FF4P1T has not been replaced.  
Please contact your customer care center for more information.

### Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Control Units	Selector switch FORWARD-OFF-REVERSE
Enclosure Type	NEMA 12 painted sheet steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	25 hp 575 V AC 3 phases 25 hp 460 V AC 3 phases
Number of Poles	3P
System Voltage	600 V AC
NEMA Size	2
Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Pilot Light	Red indicator on incandescent
Starter Type	Reversing
Overload Type	Melting alloy
Number of Thermal Units Required	3
Disconnect Type	Fusible disconnect R 60 A

### Ordering and shipping details

Category	21292 - 8738,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	105
Returnability	N

### Contractual warranty

Warranty period	18 months
-----------------	-----------