

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 18ANEM

8739SBA52V84A1F4T

! Discontinued

Main

Control Circuit	Control circuit transformer
Device Short Name	S

Complementary

Control Type	selector switch FORWARD-REVERSE-STOP
Depth	10.09 in (256.29 mm)
Device Mounting	Surface
Height	24.75 in (628.65 mm)
Maximum Horse Power Rating	0.5...1 hp 200/230 V AC 1.5...3 hp 460/575 V AC
Motor Starter Type	Reversing
Nema Size	0
Number Of Poles	3
Number Of Thermal Units Required	3
Primary Voltage	208 V AC 60 Hz
Product Destination	Circuit breaker GJL36007M02
Net Weight	52 lb(US) (23.59 kg)
Reset	With external
Secondary Voltage	120 V AC 60 Hz
Width	13.75 in (349.25 mm)

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	NEMA UL Listed

Ordering and shipping details

Category	21291-8738,39SB(NOT S*R,S*T,S*W)
Discount Schedule	CP1
Returnability	No

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	60.00 lb(US) (27.216 kg)

Contractual warranty

Warranty	18 months
----------	-----------