

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 27ANEM

8739SCA51V83SY74

! Discontinued

Main

Device Short Name	S
-------------------	---

Complementary

Depth	10.09 in (256.29 mm)
Device Mounting	Surface
Height	24.75 in (628.65 mm)
Maximum Horse Power Rating	0.25...0.34 hp 200/230 V AC 0.25...1 hp 460/575 V AC
Motor Starter Type	Reversing
Nema Size	1
Number Of Poles	3
Number Of Thermal Units Required	3
Primary Voltage	480 V AC 60 Hz
Product Destination	Circuit breaker GJL36003M01
Net Weight	52 lb(US) (23.59 kg)
Reset	With external
Secondary Voltage	24 V AC 60 Hz
Width	13.75 in (349.25 mm)

Environment

Nema Degree Of Protection	NEMA 12
Product Certifications	NEMA UL Listed

Ordering and shipping details

Category	21292-8738,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	60.00 lb(US) (27.216 kg)
------------------	--------------------------

Contractual warranty

Warranty	18 months
----------	-----------