

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 45A NEM

8739SDA52V06

 To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

 To be discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Common control circuit
Control Units	No control units
Enclosure Type	NEMA 12 painted sheet steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	5 hp 200 V AC 5...7.5 hp 230 V AC 10...15 hp 460 V AC 15...20 hp 575 V AC
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Nema Size	2
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	melting alloy
Number Of Thermal Units Required	3
Disconnect Type	Mag-Gard circuit breaker

Ordering and shipping details

Category	21292 - 8738,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	95.00 lb(US) (43.091 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation