

Product data sheet

Specifications

SQUARE D



REVERSING COMBO STARTER 600VAC 45A NEM

8739SDA52V81FF4T

Price*: 5,831.00 USD

! Discontinued

Main

Product	Combination Starter
Type	S
Control Circuit Type	Control circuit transformer
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Control Units	No control units
Enclosure Type	NEMA 12 painted sheet steel with external reset
Auxiliary Contacts	Without
Horsepower Rating	5 hp 200 V AC 5...7.5 hp 230 V AC 10...15 hp 460 V AC 15...20 hp 575 V AC
Number Of Poles	3P
Maximum Voltage Rating	600 V AC
Nema Size	2
Control Circuit Voltage	480 V AC 60 Hz primary circuit 120 V AC 60 Hz secondary circuit
Pilot Light	No indicator
Starter Type	Reversing
Overload Type	melting alloy
Number Of Thermal Units Required	3
Disconnect Type	Mag-Gard circuit breaker

Ordering and shipping details

Discount Schedule	CP1
Returnability	No

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	100.00 lb(US) (45.359 kg)

Contractual warranty

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months