## Product data sheet

Specifications



## Contactor, Type L, multipole lighting, electrically held, 30A, 2 pole, 600 V, 440/480 VAC 50/60 Hz coil, NEMA 3R/12

8903LA20V06

(!) To be discontinued on: Sep 30, 2024

# Product availability: Non-Stock - Not normally stocked in distribution facility

#### Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit
Complementary	
Control Circuit Voltage	440 V AC 50 Hz 480 V AC 60 Hz
Inrush Power In Va	150 VA 60 Hz 150 VA 50 Hz
Hold-In Power Consumption In Va	30 VA 60 Hz 30 VA 50 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	2P 2 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical Connection	Screw-clamp terminals
Height	15.75 in (400 mm)
Depth	8.50 in (216 mm)

### Environment

Width

Enclosure Type	NEMA 12 painted sheet steel surface
Product Certifications	UL Listed CSA

8.11 in (206 mm)

### Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Price is "List Price" and may be subject to a trade discount - check with your local distributor or retailer for actual price.

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.75 in (40.0 cm)
Package 1 Width	8.11 in (20.6 cm)
Package 1 Length	8.50 in (21.6 cm)
Package 1 Weight	21.78 lb(US) (9.88 kg)

## **Contractual warranty**

Warranty

18 months

## Sustainability Screen Premium

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

## Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes
Pvc Free
Halogen Free Plastic Parts Product

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations