

# Product data sheet

## Characteristics

# 8903LA30V01

8903L electrically held lighting contactor, 3 P, 3 NO, 30 A, 600 V, 24 V 60 Hz c

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\* : 903.00 USD



### Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

### Complementary

Control Circuit Voltage	24 V AC 60 Hz
Inrush power in VA	150 VA 60 Hz
Hold-in power consumption in VA	30 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	3P 3 NO
Control Unit	No control units
Pilot Light	No indicator
Electrical connection	Screw-clamp terminals
Height	15.75 in (400 mm)
Depth	8.5 in (216 mm)
Width	8.11 in (206 mm)

### Environment

Enclosure Type	NEMA 12 painted sheet steel and with surface Mounting;
Product certifications	CSA UL listed

### Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1

GTIN	00785901778189
Nbr. of units in pkg.	1
Package weight(Lbs)	21.780000000000001
Returnability	N
Country of origin	MX

### Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
------------------------	--

### Contractual warranty

Warranty period	18 months
-----------------	-----------