

Contactor, Type L, multipole lighting, electrically held, 30A, 2 pole, 600 V, 277 VAC 60 Hz coil, NEMA 1 flush

8903LF20V04

! To be discontinued on: Sep 30, 2024

Product availability: Non-Stock - Not normally stocked in distribution facility

Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	277 V AC 60 Hz	
Inrush Power In Va	150 VA 60 Hz	
Hold-In Power Consumption In Va	30 VA 60 Hz	
Current Rating	20 A tungsten 30 A fluorescent	
Number Of Poles	2P 2 NO	
Control Unit	No control units	
Pilot Light	No indicator	
Electrical Connection	Screw-clamp terminals	
Height	15.20 in (386 mm)	
Depth	5.43 in (138 mm)	
Width	8.94 in (227 mm)	

Environment

Enclosure Type	NEMA 1 painted sheet steel flush
Product Certifications	UL Listed CSA

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Returnability	No
Country Of Origin	MX

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.20 in (38.6 cm)
Package 1 Width	8.94 in (22.7 cm)
Package 1 Length	5.43 in (13.8 cm)
Package 1 Weight	39.42 lb(US) (17.88 kg)

Contractual warranty

Warranty 18 months



Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance

⊘	Reach Free Of Svhc
⊘	Toxic Heavy Metal Free
②	Mercury Free
9	Rohs Exemption Information Yes
⊘	Pvc Free
9	Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations