

# Product data sheet

Specifications

SQUARE D



## LIGHTING CONTACTOR 600VAC 30A L

8903LG20V81CF4P1T

Price\*: 1,373.00 USD

! Discontinued

### Main

Product Or Component Type	Electrically Held Lighting Contactor
Range Of Product	8903L
Control Circuit	Control circuit transformer

### Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	2P 2 NO
Control Unit	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Control Circuit Fusing	2 fuses primary circuit
Electrical Connection	Screw-clamp terminals

### Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

### Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	40.30 lb(US) (18.28 kg)

### Contractual warranty

Warranty	18 months
----------	-----------

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications