


Price* : 2,591.00 USD



8903LG30V84CFF4K14T has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Control circuit transformer

Complementary

Control Circuit Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	3P 3 NO
Control Unit	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	24-hour time clock
Electrical connection	Screw-clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel and with surface Mounting;
Product certifications	CSA UL listed

Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	40.52000000000003
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------