


Price* : 2,384.00 USD



8903LG40V02G101K142 has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

Complementary

Control Circuit Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	4P 4 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	7-day time clock
Electrical connection	Screw-clamp terminals

Environment

Enclosure Type	NEMA 1 painted sheet steel and with surface Mounting; with photoelectric receptacle with cell
Product certifications	CSA UL listed

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	22.440000000000001
Returnability	N
Country of origin	MX

Contractual warranty

Warranty period	18 months
-----------------	-----------