

# Product data sheet

## Characteristics

# 8903LW80V04CF

8903L electrically held lighting contactor, 8 P, 8 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 4/4X, stainless steel

Product availability : Non-Stock - Not normally stocked in distribution facility



Price\*\* : 2,179.00 USD



### Main

Product or component type	Electrically Held Lighting Contactor
Range of product	8903L
Control Circuit	Separate control circuit

### Complementary

Control Circuit Voltage	277 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz
Hold-in power consumption in VA	35 VA 60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	8P 8 NO
Control Unit	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Control Circuit Fusing	1 fuse
Electrical connection	Screw-clamp terminals
Height	14.69 in (373 mm)
Depth	7.80 in (198 mm)
Width	12.64 in (321 mm)

### Environment

Enclosure Type	NEMA 4/4X brushed stainless steel surface
Product certifications	UL listed CSA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications.

## Ordering and shipping details

Category	21321 - 8903 L (NOT LX)
Discount Schedule	CP1
Package weight(Lbs)	10.08 kg (22.22 lb(US))
Returnability	No
Country of origin	MX

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information.
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------