

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 3 P, 3 NO, 30 A, 600 V, 277/120 V 60 Hz, NEMA 1

8903LXG30V85FF4R6T

Price*: 1,664.00 USD

Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 277 V AC 60 Hz primary circuit
Inrush Power In Va	150 VA 60 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	3P 3 NO
Control Unit	No control units
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	2P relay (1 NO + 1 NC)
Electrical Connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	61.91 lb(US) (28.08 kg)

Contractual warranty

Warranty	18 months
----------	-----------