

8903LXG40V81CF4R6T

8903LX mechanically held lighting contactor, 4 P, 4 NO, 30 A, 600 V, 480/120 V 60 Hz, NEMA 1



Price** : 1,715.00 USD



8903LXG40V81CF4R6T has not been replaced. Please contact your customer care center for more information.

Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 480 V AC 60 Hz primary circuit
Inrush power in VA	150 VA 60 Hz 25 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	4P 4 NO
Control Unit	Selector switch (HAND-OFF-AUTO)
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	Painted sheet steel NEMA 1 and with surface Mounting;
Product certifications	CSA UL listed

Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
----------	-------------------------

Discount Schedule	CP1
Nbr. of units in pkg.	1
Package weight(Lbs)	61.910000000000004
Returnability	N
Country of origin	MX

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------