

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 4 P, 4 NO, 30 A, 600 V, 208/120 V 60 Hz, NEMA 1

8903LXG40V84A3FF4T

Price*: 1,665.00 USD

! Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Control circuit transformer

Complementary

Control Voltage	120 V AC 60 Hz secondary circuit 208 V AC 60 Hz primary circuit
Inrush Power In Va	150 VA 60 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	4P 4 NO
Control Unit	Push-button ON) Push-button OFF)
Pilot Light	No indicator
Control Circuit Fusing	2 fuses primary circuit 1 fuse secondary circuit
Other Options	None
Electrical Connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	57.72 lb(US) (26.18 kg)

Contractual warranty

Warranty	18 months
----------	-----------