

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 110/120 V 50/60 Hz coil, NEMA 1

8903LXG60V02CNP1R6

Price*: 2,177.00 USD

! Discontinued

Main

Product Or Component Type	Mechanically Held Lighting Contactor
Range Of Product	8903LX
Control Circuit	Separate control circuit

Complementary

Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush Power In Va	180 VA 60 Hz 170 VA 50 Hz 170 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number Of Poles	6P 6 NO
Control Unit	Selector switch HAND-OFF-AUTO)
Pilot Light	Red indicator on incandescent
Other Options	2P relay (1 NO + 1 NC) Solid neutral terminal block
Electrical Connection	Screw-clamp terminals
Height	11.89 in (302 mm)
Depth	7.44 in (189 mm)
Width	11.89 in (302 mm)

Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product Certifications	UL Listed CSA

Ordering and shipping details

Discount Schedule	CP1
Returnability	No
Country Of Origin	US

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Weight	44.93 lb(US) (20.38 kg)

Contractual warranty

Warranty	18 months
----------	-----------