

# Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 110/120 V 50/60 Hz coil, NEMA 1

8903LXG60V02N

Price\*: 1,272.00 USD

! Discontinued

## Main

|                           |                                      |
|---------------------------|--------------------------------------|
| Product Or Component Type | Mechanically Held Lighting Contactor |
| Range Of Product          | 8903LX                               |
| Control Circuit           | Separate control circuit             |

## Complementary

|                       |                                                 |
|-----------------------|-------------------------------------------------|
| Control Voltage       | 110 V AC 50 Hz<br>120 V AC 60 Hz                |
| Inrush Power In Va    | 180 VA 60 Hz<br>170 VA 50 Hz<br>170 VA 50/60 Hz |
| Current Rating        | 20 A tungsten<br>30 A fluorescent               |
| Number Of Poles       | 6P 6 NO                                         |
| Control Unit          | No control units                                |
| Pilot Light           | No indicator                                    |
| Other Options         | Solid neutral terminal block                    |
| Electrical Connection | Screw-clamp terminals                           |
| Height                | 12.68 in (322 mm)                               |
| Depth                 | 6.02 in (153 mm)                                |
| Width                 | 7.80 in (198 mm)                                |

## Environment

|                        |                                    |
|------------------------|------------------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel surface |
| Product Certifications | UL Listed<br>CSA                   |

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

## Packing Units

|                              |     |
|------------------------------|-----|
| Unit Type Of Package 1       | PCE |
| Number Of Units In Package 1 | 1   |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                  |                         |
|------------------|-------------------------|
| Package 1 Weight | 39.86 lb(US) (18.08 kg) |
|------------------|-------------------------|

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|