

Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 277 V 60 Hz coil, NEMA 1

8903LXG60V04CF4R62

Price*: 2,406.00 USD

! Discontinued

Main

| | |
|---------------------------|--------------------------------------|
| Product Or Component Type | Mechanically Held Lighting Contactor |
| Range Of Product | 8903LX |
| Control Circuit | Separate control circuit |

Complementary

| | |
|------------------------|--|
| Control Voltage | 277 V AC 60 Hz |
| Inrush Power In Va | 180 VA 60 Hz 170 VA 50/60 Hz |
| Current Rating | 20 A tungsten 30 A fluorescent |
| Number Of Poles | 6P 6 NO |
| Control Unit | Selector switch HAND-OFF-AUTO) |
| Pilot Light | No indicator |
| Control Circuit Fusing | 2 fuses |
| Other Options | 3-wire long-distance control interface |
| Electrical Connection | Screw-clamp terminals |
| Height | 12.68 in (322 mm) |
| Depth | 6.02 in (153 mm) |
| Width | 7.80 in (198 mm) |

Environment

| | |
|------------------------|------------------------------------|
| Enclosure Type | NEMA 1 painted sheet steel surface |
| Product Certifications | UL Listed CSA |

Ordering and shipping details

| | |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability | No |
| Country Of Origin | US |

Packing Units

| | |
|------------------------------|-----|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------|-------------------------|
| Package 1 Weight | 44.27 lb(US) (20.08 kg) |
|------------------|-------------------------|

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|