

# Product data sheet

Specifications

SQUARE D



8903LX mechanically held lighting contactor, 6 P, 6 NO, 30 A, 600 V, 277/120 V 60 Hz, NEMA 1

8903LXG60V85F4T

Price\*: 1,544.00 USD

! Discontinued

## Main

|                           |                                      |
|---------------------------|--------------------------------------|
| Product Or Component Type | Mechanically Held Lighting Contactor |
| Range Of Product          | 8903LX                               |
| Control Circuit           | Control circuit transformer          |

## Complementary

|                        |                                                                    |
|------------------------|--------------------------------------------------------------------|
| Control Voltage        | 120 V AC 60 Hz secondary circuit<br>277 V AC 60 Hz primary circuit |
| Inrush Power In Va     | 180 VA 60 Hz<br>170 VA 50/60 Hz                                    |
| Current Rating         | 20 A tungsten<br>30 A fluorescent                                  |
| Number Of Poles        | 6P 6 NO                                                            |
| Control Unit           | No control units                                                   |
| Pilot Light            | No indicator                                                       |
| Control Circuit Fusing | 2 fuses primary circuit                                            |
| Other Options          | None                                                               |
| Electrical Connection  | Screw-clamp terminals                                              |
| Height                 | 11.89 in (302 mm)                                                  |
| Depth                  | 7.44 in (189 mm)                                                   |
| Width                  | 11.89 in (302 mm)                                                  |

## Environment

|                        |                                    |
|------------------------|------------------------------------|
| Enclosure Type         | NEMA 1 painted sheet steel surface |
| Product Certifications | UL Listed<br>CSA                   |

## Ordering and shipping details

|                   |     |
|-------------------|-----|
| Discount Schedule | CP1 |
| Returnability     | No  |
| Country Of Origin | US  |

## Packing Units

|                        |     |
|------------------------|-----|
| Unit Type Of Package 1 | PCE |
|------------------------|-----|

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                              |                         |
|------------------------------|-------------------------|
| Number Of Units In Package 1 | 1                       |
| Package 1 Weight             | 12.00 lb(US) (5.443 kg) |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|